



## HD-7L LED DTE-Woodpecker handpiece for scaling unit, Satelec compatible

White LED handpiece for Woodpecker power scaling unit, Satelec compatible

**Available**

**SKU:** M17SL

**Categories:** Professional Equipment, Scaler Handpieces



### Description

The **HD-7L LED DTE-Woodpecker scaler handpiece** is a high-quality piezoelectric instrument designed to ensure reliability, precision, and durability. Its lightweight and ergonomic design allows the operator to work comfortably, reducing hand fatigue even during long procedures. Thanks to the integrated optical fiber with LED light, it guarantees a clear and well-illuminated working field, enhancing clinical accuracy.

Made of materials highly resistant to high temperatures and pressure, this handpiece can be sterilized in an autoclave without cracks or deformations, ensuring constant hygiene and safety.

Fully compatible with the Satelec® connection system, it can be used with all Satelec® and Satelec® LED compatible tips, offering maximum versatility and adaptability for professional use. The ultrasonic transducer ensures mechanical strength and stable performance, supported by CE certification for guaranteed quality.

With a working frequency of 28KHz  $\pm$ 3KHz and a luminous intensity of 7,000 lux, the HD-7L LED handpiece provides consistent results, operator comfort, and excellent visibility. It is the perfect tool for dental practices and clinics seeking ergonomics, compatibility, and reliable performance over time.

Technical features HD-7L LED DTE scaler handpiece

Version	Scaler handpiece
Tip compatibility	Satelec®



Coupling compatibility	Satelec® LED
Color handpiece	White
Optic fibre	Yes
Light intensity (lux)	7.000
Ultrasonic frequency	28KHz +/- 3KHz
Ultrasonic transducer type	Ultrasonic
Dimensions (lxØ mm)	111 x 20,5
Handpiece weight (g)	63
Cord length (meters)	/
Autoclavable	Yes
Warranty	12 months
CE	0197