



## HD-7L LED DTE-Woodpecker handpiece for scaling unit, Satelec compatible

White LED handpiece for Woodpecker power scaling unit, Satelec compatible

**Shipping expected in approximately 30 days**

**SKU:** M17SL

**Categories:** Scaler Handpieces



### Description

The **HD-7L LED DTE-Woodpecker piezoelectric scaler handpiece** is a professional instrument designed to provide operating precision, reliability and comfort during ultrasonic scaling, oral hygiene and dental prophylaxis procedures. The integrated LED light makes it particularly suitable for treatments requiring enhanced visibility of the operating field.

Thanks to its **lightweight and ergonomic design**, the handpiece fits comfortably in the operator's hand, ensuring a stable and secure grip even during prolonged use. Its balanced shape helps reduce hand fatigue and improves movement control throughout the procedure.

The **integrated LED light with optical fibre** provides a clear and direct view of the working area, supporting greater precision during treatment. This feature helps the operator manage daily procedures more accurately and maintain better control of the clinical field.

Manufactured from materials resistant to high temperatures and sterilisation pressure, the HD-7L LED handpiece is **autoclavable**, maintaining structural integrity, safety and hygiene over time, even after repeated sterilisation cycles.

Compatible with the **Satelec® system**, the handpiece can be used with **Satelec® and Satelec® LED compatible tips**, making it easy to integrate with existing dental equipment. This compatibility makes it a versatile solution for dental practices and clinics using widely adopted piezoelectric systems.

Reliable, practical and functional, the **HD-7L LED DTE-Woodpecker scaler handpiece** is a professional choice both as a replacement part and as a new handpiece to add to existing equipment, offering operating comfort, improved visibility and consistent performance.

### Technical features HD-7L LED DTE scaler handpiece



Version	Scaler handpiece
Tip compatibility	Satelec®
Coupling compatibility	Satelec® LED
Color handpiece	White
Optic fibre	Yes
Light intensity (lux)	7.000
Ultrasonic frequency	28KHz +/- 3KHz
Ultrasonic transducer type	Ultrasonic
Dimensions (lxØ mm)	111 x 20,5
Handpiece weight (g)	63
Cord length (meters)	/
Autoclavable	Yes
Warranty	12 months
CE	0197