



HW-5L LED Woodpecker white handpiece for scaling unit, EMS compatible

White LED handpiece for Woodpecker power scaling unit, EMS compatible

Available from 31/07/2025

SKU: M16AL

Categories: Handpieces



Description

HW-5L LED Woodpecker handpiece for scaling unit.

High quality handpiece for powerscaling unit, sterilizable in autoclave, with fiber optic.

Lightweight and ergonomic design for convenient working without fatigue

Ems® compatible.

Technical features HW-5L LED Woodpecker handpiece for scaling unit.

| | |
|------------------------|------------------|
| Version | Scaler handpiece |
| Tip compatibility | Ems® |
| Coupling compatibility | EMS® LED |
| Color handpiece | White |



| | |
|----------------------------|----------------|
| Optic fibre | Yes |
| Light intensity (lux) | 7.000 |
| Ultrasonic frequency | 28KHz +/- 3KHz |
| Ultrasonic transducer type | Ultrasonic |
| Dimensions (lxØ mm) | 100 x 20 |
| Handpiece weight (g) | 52 |
| Cord length (meters) | / |
| Autoclavable | Yes |
| Warranty | 12 months |
| CE | 0197 |