



HW-6L LED Woodpecker handpiece, EMSsine wave drive compatible

White LED handpiece HW-6L for powerscaling unit, EMS compatible.

Available from 16/09/2025

SKU: M16UL

Categories: Handpieces

Description

HW-6L LED Woodpecker handpiece.

High quality handpiece for powerscaling unit, sterilizable in autoclave, with fiber optic.

Lightweight and ergonomic design for convenient working without fatigue

Ems® compatible.

Technical features HW-6L LED Woodpecker handpiece.

Version	Scaler handpiece
Tip compatibility	Ems®
Coupling compatibility	EMS® LED Sine-wave drive
Color handpiece	White



Optic fibre	Yes
Light intensity (lux)	7.000
Ultrasonic frequency	28KHz +/- 3KHz
Ultrasonic transducer type	Ultrasonic
Dimensions (lxØ mm)	100 x 20
Handpiece weight (g)	52
Cord length (meters)	/
Autoclavable	Yes
Warranty	12 months
CE	0197