



## DTE-Woodpecker AP-B dental scaler and air polisher, SATELEC compatible

AP-B Woodpecker benchtop power scaling unit with Air Polisher, LED, SATELEC compatible.

**Available**

**SKU:** SCR40APB

**Categories:** Benchtop scalers

### Description

DTE-Woodpecker AP-B dental scaler and air polisher.

AP-B Ultrasonic Scaler + Aeropulper Woodpecker is the stand-alone unit dedicated to oral hygiene. It synergistically combines essential tools for dental prophylaxis: a painless piezoelectric scaler and a whitener. Designed for intensive professional use, it offers an efficient and comfortable treatment for the patient. It stands out for its irreverent design and unparalleled practicality. The complete solution for perfect prophylaxis.

#### Main Features of DTE-Woodpecker AP-B dental scaler and air polisher:

- Compatible with SATELEC (hose connection and threaded tips), with LED light.
- Adjustable working frequency up to 35,000 Hz.
- Working range of motion: 90°.
- 3 programs: Cleaning, periodontics and endodontics.
- HW-5L detachable and autoclavable handpiece.
- Water supply: autonomous.
- Includes: 6-point and self-limiting spanner.

#### Main Features of the AP-B Aeropulper:

- Powerful and versatile 2 IN 1 aeropulper: Supragingival function and subgingival function.
- Completely transparent bottle and funnel.
- Inlet air pressure: 5.5 – 7.5 bar.
- Lightweight and compact desktop unit: 2,0 kg / 27 x 17 x 9 cm
- Designed for use with Bicarbonate and Glycine powders (recommended sizes 65 µm. and 25 µm. respectively).



- **Includes:** Bircarbonate bottle, Glycine bottle, 10 Subgingival tips, tip spanner and two sterilisation boxes.
- **Guarantee:** 24 months (12 months for the handpiece).
- **Two handpieces:**
  - Supragingival treatment handpiece
  - Subgingival treatment handpiece

**Technical features of the handpiece:**

- Lightweight.
- With small tip for better visibility and more precise prophylaxis.
- Separable into 3 parts.
- 360° rotation.
- Subgingival tip:
- Made of medical polymers.
- Flexible.
- Dust outlet in three directions and water outlet in one direction.
- In-depth plaque removal.
- Great accessibility.