



Printed on 02/06/2025

<https://shop.tecnomeditalia.com/en/product/x-ray-ac-70-kv-maximum-extension-213-cm/>



X-ray AC 70 KV, maximum extension 213 cm

Tecnomed dental wall X-ray unit, AC 70kv, with radio frequency remote control, arm extension 2130 mm.

2.500,08 €

Available on request

SKU: DE72RX

Categories: X-ray machines

Description

The Tecnomed Italia intraoral X-ray unit wall mounted AC with a 2130mm arm is designed to deliver reliable performance and enhanced safety during dental radiographic procedures. This device simplifies chairside imaging, offering precise and high-quality results at a competitive price.

Compact Design and Advanced Technology

AC intraoral X-ray unit features a compact and lightweight design, with all functions integrated into the monoblock. The device guarantees sharp, high-resolution images, thanks to advanced Italian electronics and rigorous quality testing. The radiogenic head is angled for easy alignment, while the automatic termoswitch system enhances safety during operation, protecting both the operator and the patient.

Enhanced Safety with Wireless Remote Control

This unit is equipped with a wireless remote control, allowing the operator to conduct the radiographic procedure from outside the room, ensuring safe and accurate imaging. The radiogenic head is also equipped with a goniometer, providing additional precision in positioning. The lightweight, self-balancing pantograph arm ensures excellent maneuverability and stability during use.

Adaptable and Pre-Programmed Functions

The control panel, integrated into the monoblock, includes pre-programmed functions for various anatomical conditions. These settings can be easily adjusted, allowing for quick and practical selection of exposure parameters, optimizing the unit's performance for every patient.

Ideal for Dental Practices

The AC intraoral X-ray unit is ideal for dental practices that require a reliable, user-friendly, and cost-effective solution without compromising on image quality or operational safety. It is an excellent choice for professionals looking to integrate an efficient and safe intraoral radiography system into their

practice.

Technical features intraoral X-ray unit wall mounted AC with a 2130mm arm.

Installation	wall mounted
Extension	133+80 cm
Arm lenght	80 cm
Kv	70
Anodic current	8 mA
Filtration mm	2 AL
X-ray control	Wireless CE0051
Exposure time	0,040 – 2 sec
Focal distance	20 cm
Cone diameter	6 cm
Power supply	230/240V-50Hz
Weight head	6 Kg
Color	RAL 9010
Warranty	24 months